

5095 Performance Resin

Ribbon	Ribbon Type		Compatible Material	Print Speed		Temperature Resistance				Smear/Scratch Resistance				Chemical Resistance								
2300	Wax	Standard	Uncoated/Coated Paper																			
2100	Wax	High-Performance	Uncoated/Coated Paper																			
3400	Wax/Resin	High-Performance	Uncoated/Coated Paper Matte Synthetics																			
3200	Wax/Resin	Premium	Uncoated/Coated Paper Matte Synthetics																			
4800	Resin	Performance	Matte/Gloss Synthetics																			
5095	Resin	High-Performance	Matte/Gloss Synthetics																			
5100	Resin	Premium	Matte/Gloss Synthetics																			
lmage Lock™	Resin	Specialist	Z-Xtreme™ 5000T																			

Additional Features

- High-performance resin ribbon for use on matte and gloss synthetics
- Provides excellent print quality, even with small fonts, graphics and rotated barcodes
- Excellent chemical resistance and performance in most harsh environments
- Excellent temperature resistance, and smear and scratch resistance on both matte and gloss synthetics

Suggested Applications

- Labels exposed to heat, steam, solvents, abrasion and friction
- Outdoor labelling applications in extreme environments
- Chemical container labels
- Automotive labels
- Industrial rating plates

UL Recognised and CSA Certified

UL and CSA approved for use with the following materials:

- Z-Ultimate® 3000T White
- Z-Ultimate® 3000T Silver
- Z-Xtreme[™] 4000T White
- Z-Xtreme™ 4000T White High-Tack
- Z-Xtreme[™] 4000T Silver High-Tack





UL approved for use with the following materials:

- Z-Ultimate® 2500T White
- Z-Ultimate® 3000T Yellow
- Z-Ultimate® 3000T High-Tack
- 8000T Void Matte

Technical Specifications

	Description
Colour	Black
Base Film	Polyester
Base Film Caliper	4.5 microns
Total Caliper	6.2 microns ±10%
Scanning Capabilities	IR and Visible Light

Ribbon Compliance

Compliance	5095
REACH/ Substances of Very High Concern (SVHC)	✓
RoHS	✓
Dodd-Frank Act (Conflict Minerals)	✓
Toxic Substances Control Act of 1976	✓
Carcinogenic, Mutagenic and Reprotoxic, or Substances Toxic Substances 1976/769/ EC	
California Proposition 65	✓
FDA 21 CFR Part 175.300 – Indirect Food Contact – Resinous and Polymeric Coatings	✓
European Food Directive 1935/2004/EC	✓
Foodstuffs and Consumer Goods Act and LFGB approved	✓
Halogen free	✓
Latex free	✓
Animal derivatives free	✓
BP Free	✓

©2015 ZIH Corp. All rights reserved.



Stocked Sizes Available for the following Zebra Printers:	P4T, desktop, mid-range and high- performance thermal printers, Zebra engines, other legacy Zebra printers (Other widths/lengths are available on request subject to minimum order quantities and lead times)
	Note: P4T ribbons are only available in cartridge form at 110mm wide and 30 meters in length.
Recommended Storage Conditions:	1 year duration when stored at -5°C to 40°C at 20% to 85% RH

5095 Barcode Scannability

The below scannability testing was performed on 140XiII, 170XiIII, 105SI and Z4Mplus.

Label Facestock	Print Speed	Barcode	Lab Results
Synthetics	Up to 203.2mm/sec	10 or 12 mil normal code	Typical ANSI Grade A
Synthetics	Up to 152.4mm/sec	15 mil rotated code	Typical ANSI Grade B



Performance Analysis

All of the below tests were performed on Z-Xtreme[™] 4000T White using 10 cycles (20 rubs) with the Crockmeter.

Zebra 5095 Performance
✓
✓
✓
٨
✓
✓
✓
٨
✓

✓: Scanning received a "B" ANSI grade or above.

A : Scanning received a "C" to "F" ANSI grade.

Blank: Barcode does not scan

Product Performance and Suitability

The information contained in this document is to be used for guidance only and is not intended for use in setting specifications. All purchasers of Zebra products shall be solely responsible for independently determining if the product conforms to all requirements of their unique application.

All products should be pre-tested to ensure they meet all intended requirements of specific end-use applications.

For testing of this ribbon on Zebra mid-range and high-performance printers please order part number 05095BK11005. For testing on other printer models, please contact your Supplies Specialist representative.